

[See all 10 Products in Family](#)

255mm, 1030-1080nm + VIS JENar™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock **#17-025** 8 In Stock

-

1

+

C\$2,814^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,814.00 each
Need More?	Request Quote

Product Downloads

General	
601948	Model Number:
JENar F-Theta	Type:
Note: + VIS options provide >85% Transmission from 500-680nm	
#17-697: One Included	Protective Window:
Manufacturer:	

Jenoptik	
Physical & Mechanical Properties	
119.8 +0/-0.2	Maximum Diameter (mm):
1400	Weight (g):
336	Flange Distance (mm):
20	Input Beam Diameter, 1/e ² (mm):
65.3	Maximum Length (mm):
Optical Properties	
255.00	Focal Length FL (mm):
53.2	Scan Angle (°):
169 x 169	Scan Field (mm):
F-Theta Only: 14.3 With Scanner: 15	Telecentricity (°):
291	Working Distance (mm):
500 - 680, 1030 - 1080	Wavelength Range (nm):
239	Scan Field Diameter (mm):
24	Focus Size Diameter, 1/e ² (µm):
3670	GDD Specification (fs ²):
Threading & Mounting	
M85 x 1	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.