


TECHSPEC® 25.4mm Diameter x 250mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens



Stock #11-623 ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$254.80

ADD TO CART

Qty 1-5

C\$254.80

Qty 6+

C\$222.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
250.29 @ 587.6nm

Back Focal Length BFL (mm):
249.19

Coating: BBAR (1900-2200nm)
Coating Specification: R_{abs} <0.15% @ 1900 - 2200nm
Substrate: Fused Silica IR Grade
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 0.9
Radius R₁ (mm): 114.75
Clear Aperture CA (mm): 22.86
f/#: 9.85
Numerical Aperture NA: 0.051
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1900 - 2200
Angle of Incidence (°): 0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View