

25.4mm Dia. x 63.5mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) DCX Lens |CF-BX-25-63

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#48-018** ☐ In Stock

-

1

+

C\$368.20

ADD TO CART

Qty 1+
C\$368.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
63.50

Coating:
Uncoated

Substrate: Calcium Fluoride (CaF₂)
Surface Quality: 60-40
Clear Aperture (%) : 90.00
Centering (arcmin) : <3
Bevel: Protective bevel as needed
Center Thickness CT (mm) : 5.30
Center Thickness Tolerance (mm) : ±0.2
Edge Thickness ET (mm) : 2.00
Radius R₁=R₂ (mm) : 49.89
Back Focal Length BFL (mm) @ DWL : 61.56
Effective Focal Length EFL @ 0.6328μm (mm) : 58.57
Effective Focal Length EFL @ 1.064μm (mm) : 59.16
Effective Focal Length EFL @ 2.94μm (mm) : 60.59
Effective Focal Length EFL @ 5.0μm (mm) : 63.50
f/# : 2.5
Focal Length Specification Wavelength (μm) : 5.00
Focal Length Tolerance (%) : ±2 @ DWL
Numerical Aperture NA : 0.20
Surface Accuracy : 1λ
Type : Double-Convex Lens
Wavelength Range (μm) : 0.35 - 7
Wavelength Range (nm) : 350 - 7000
Model Number : CF-BX-25-63

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View