

254mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock **#15-182** ☐ In Stock

1 **C\$1,712.20**

ADD TO CART

Qty 1-4
C\$1,712.20
Qty 5+
C\$1,541.40
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
254.00

Maximum Diameter (mm):
122

Scan Angle (°):
±25.00

Scan Field (mm): 157.0 x 157.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 304.6
Wavelength Range (nm): 1064
Range Distance (mm): 360.6
Focus Size Diameter, 1/e² (μm): 25
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 76.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View