

TECHSPEC® 25.4mm H x 25.4mm L x 250mm FL NIR I, Illumination Grade PCX Cylinder Lens



Stock **#36-235** ☐ In Stock

-

1

+

C\$123.20

ADD TO CART

Qty 1-5
C\$123.20
Qty 6+
C\$98.70
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
250.00

Substrate: ☐
[N-BK7](#)

f/#:
9.84251968503937

Numerical Aperture NA:

0.05
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 248.02
Center Thickness CT (mm): 1.94
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 129.20
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant