

25.4mm, ISP Optics Zinc Selenide Equilateral Prism | ZC-EP-25

See More by [ISP Optics](#)



Stock **#19-714** ☒ In Stock

1 **C\$3,171.00**

ADD TO CART

Qty 1-5
C\$3,171.00
Qty 6+
C\$2,536.80
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
Zinc Selenide (ZnSe)

Surface Quality:
60-40

Type: Equilateral Prism
Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85
Length of Hypotenuse (mm): 25.40
Length of Legs (mm): 25.40
Wavelength Range (nm): 600 - 18000
Wavelength Range (µm): 0.6 - 18
Surface Flatness (P-V): 2λ
Model Number: GE-EP-25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View