

TECHSPEC® 25mm, 200-600mm Primary WD, HR Series Fixed Focal Length Lens



25mm Focal Length



Stock **#63-780** ☐ In Stock



1



C\$1,190.00

ADD TO CART

Qty 1+

C\$1,190.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
40.99

Horizontal Field of View, 1/2" Sensor:
55.9mm - 14.5°

Horizontal Field of View, 2/3" Sensor:
77mm - 19.9°

Filter Thread: M25.5 x0.50 (Female)
Maximum Diameter (mm): 37.5
Weight (g): 96
Horizontal Field of View, 1/3" Sensor: 41.9mm - 10.9°
Maximum Rear Protrusion (mm): 1.24
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0301
Horizontal Field of View @ Max Sensor Format: 77mm - 19.9°
Number of Elements (Groups): 9 (6)
Horizontal Field of View, 1/1.8" Sensor: 62.9mm - 16.3°
Horizontal Field of View, 1/2.5" Sensor: 49.8mm - 13.0°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.115
Maximum Sensor Format: 2/3"
Working Distance (mm): 200 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/22
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 18.3
Horizontal Field of View, 1/4" Sensor: 31.4mm - 8.2°
Object Space Principal Plane (mm): 30.89
Image Space Principal Plane (mm): -12.69
Field of View at Max Sensor Format: Horizontal: 77mm - 19.9° Vertical: 57.7mm - 15° Diagonal: 96.3mm - 24.7°
Maximum Distortion (%): 0.64
Exit Pupil Position (mm): -38.04
Optimized Working Distance (mm): 200 - 600
Lens Wavelength Range: VIS
Imaging Lens Type: High Performance Lens
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View

