

TECHSPEC®

25mm Dia., 0.83 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-962-INK** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ C\$712⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$712.60 each
Qty 6-10	C\$641.20 each
Qty 11-25	C\$583.80 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

25.00 ±0.025

Centering (arcmin):

<3

Clear Aperture CA (mm):

22.50

Edge Thickness ET (mm):

3.31

Center Thickness CT (mm):

10.40 ±0.10

Bevel:

Protective as needed

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

15.00 @587.6nm

Numerical Aperture NA:

0.83

Back Focal Length BFL (mm):

9.24

Substrate:

[N-SF6](#)

Asphere Figure Error, RMS @ 632.8nm:

0.4λ

Coating:

MS-EXT+ (350-700nm)

Coating Specification:

R_{avg} <0.5% @ 350 - 700nm @ ±30° AOI
R_{abs} <1.5% @ 350 - 700nm @ ±30° AOI

Surface Quality:

40-20

f#:

0.60

Wavelength Range (nm):

350 - 700

Conjugate Distance:

Infinite

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts