

TECHSPEC® 25mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock **#47-981** [CONTACT US](#)

- 1 +

C\$218.40

ADD TO CART

Qty 1-5
C\$218.40
Qty 6+
C\$191.80
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mrror

Parallelism (arcmin):

<3
Clear Aperture (%):>90
Back Surface:Ground
Reflection at DWL (%):99.5
Coating Specification: R_{abs} >99.5% @ 266nm @ 45° AOI R_{avg} >99.5% @ 263 - 268nm @ 45° AOI
Wavelength Range (nm):263 - 268
Surface Flatness (P-V):λ/10
Coating Type:Dielectric
Coating:Laser Mirror (266nm)
Design Wavelength DWL (nm):266
Diameter (mm):25.00 +0.0/-0.2
Thickness (mm):6.00 ±0.2
Angle of Incidence (°):45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 2.5 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View