

TECHSPEC® 25mm Dia., 0.83 NA, Uncoated 1550nm NIR Aspheric Lens



Stock **#17-418** ☐ In Stock

-

1

+

C\$525.00

ADD TO CART

Qty 1-5
C\$525.00
Qty 6+
C\$420.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
15.00 @ 1550nm

Numerical Aperture NA:
0.83

Back Focal Length BFL (mm):

8.67 @ 587.6nm
Substrate: N-SF6
Aspheric Design Wavelength (nm): 1550
Coating: Uncoated
Centering (arcmin): <2.5
Surface Quality: 40-20
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.35
Center Thickness CT (mm): 10.00 ±0.1
f/#: 0.6
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Asphere Figure Error, @ 632.8nm: 0.4λ RMS and 2λ PV
Power (diopters): 66.67

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View