

TECHSPEC® 25mm Dia 1550nm 45°, Laser Diode Mirror



Stock #63-157 **20+ In Stock**

- 1 + C\$215⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$215.18 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

>90	Clear Aperture (%):
Ground	Back Surface:
25.00 +0.0/-0.2	Diameter (mm):
6.00 ±0.2	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.8	Reflection at DWL (%):
Coating Specification:	
R _{abs} >99.8% @ 1550nm R _{avg} >98% @ 1440 - 1660nm	
1440 - 1660	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Dielectric Mirror (1440-1660nm)	Coating:
1550	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>


Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

PRODUCT DETAILS


- >99.8% Reflectivity at Design Wavelengths
- Excellent Broadband Performance for Range of Wavelengths
- Designed for Common Diode Lasers


TECHSPEC® Diode Laser Line Mirrors are designed to offer high reflection for the most common diode laser wavelengths. Designed for a 0° or 45° angle of incidence, these mirrors are ideal for beam-steering and folding applications.

Our line of [TECHSPEC® laser line mirrors](#) are specially designed for even the most demanding laser applications. Combining laser-quality substrates of up to 10-5 surface quality, with a dense reflective coating, and a damage threshold specific to the laser type and wavelength, these mirrors are ideal for a wide range of applications requiring precision reflectivity and incredible durability. All TECHSPEC® laser line mirrors are designed to minimize scatter loss and to be easily mounted into any optical system.




TECHNICAL INFORMATION







532nm 45° AOI High Power Laser Mirror




635/670nm 45° AOI Diode Laser Mirror




980nm 45° AOI Diode laser Mirror




1064nm 45° AOI High Power Laser Mirror










1480nm 45° AOI Diode Laser Mirror



700nm – 1100nm 45° AOI Broadband Mirror



Typical Reflectivity Curves



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS
