

25mm Dia., 473nm Laser Line Longpass Filter



Laser Line Longpass Filters

Stock **#47-502** ☒ In Stock

⊖ 1 ⊕

C\$1,043.70

ADD TO CART

Qty 1+
C\$1,043.70
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 25.00 +0.0/-0.1
Angle of Incidence (°): 0 ±2
Bandwidth (nm): >550
OD 6 Blocking Wavelength Range (nm): 383 - 473
Optical Density OD (Average): ≥6.0

Clear Aperture CA (mm): 22
Design Wavelength DWL (nm): 473
Substrate: ☐ Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Transmission (%): 93.00
Transmission Wavelength (nm): 479.1 - 1066.9
Type: Longpass Filter
Edge Steepness (nm): 2.40
Transition Width (nm): <4.7
Clear Aperture (%): 88
Durability: Environmental: ML-STD-810F, Physical: ML-C-48497A
Temperature Dependence (ppm/°C): <5
Angle Tuning Range, for 0 - 8° Shift: -0.3% of Laser Wavelength
Mount Thickness (mm): 3.5
Laser Blocking Wavelength (nm): 473
Damage Threshold, By Design: ☐ 0.5 J/cm² @ 266nm, 10ns, 10Hz 1 J/cm² @ 532nm, 10ns, 10Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View