

TECHSPEC® 25mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors



Stock #47-324 **20+ In Stock**

- 1 + C\$243.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$243.60 each
Qty 6-25	C\$214.20 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

<3

Parallelism (arcmin):

Clear Aperture (%):

>90

Ground **Back Surface:**

25.00 +0.00/-0.20 **Diameter (mm):**

6.00 ±0.20 **Thickness (mm):**

Optical Properties

10-5 **Surface Quality:**

99.5 **Reflection at DWL (%):**

Coating Specification:

$R_{abs} >99.5\%$ @ 355nm @ 45° AOI

$R_{avg} >99.5\%$ @ 351 - 358nm @ 45° AOI

351 - 358 **Wavelength Range (nm):**

$\lambda/10$ **Surface Flatness (P-V):**

Dielectric **Coating Type:**

Laser Mirror (355nm) **Coating:**

355 **Design Wavelength DWL (nm):**

45 **Angle of Incidence (°):**

Substrate:

[Fused Silica](#) (Corning 7980)

Damage Threshold, Reference:

6 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Induced Damage Threshold Specifications
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles.

TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts