

TECHSPEC® 25mm Dia. x 100mm FL, 8 - 12µm Coated, Ge Plano-Convex Lens



Stock **#69-667** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$665.00

ADD TO CART

Qty 1-5
C\$665.00
Qty 6+
C\$532.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00 @ 10.6µm

Back Focal Length BFL (mm):
99.25

Coating: BBAR (8000-12000nm)
Coating Specification: R_{avg} <3.0% @ 8 - 12μm
Substrate: □ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.74
Radius R₁ (mm): 300.39
Clear Aperture CA (mm): 24
f/#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 8000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
