

TECHSPEC® 25mm Dia. Enhanced Aluminum Coated, λ /10 ZERODUR® Mirror



Stock **#39-852** ☐ In Stock

-

1

+

C\$152.60

ADD TO CART

Qty 1-5
C\$152.60
Qty 6+
C\$121.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Surface Flatness (P-V):
 λ /10 (measured before coating)

Substrate: ☐
ZERODUR®

Back Surface:

Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 4.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant