


[See all 3 Products in Family](#)

25mm Dia., Low GDD 940/1030nm Yb-Doped Dichroic Mirrors



Yb-Doped Dichroic Mirrors

Stock **#28-972** **2 In Stock**

C\$819⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	C\$819.00 each
Qty 6-25	C\$695.80 each
Need More?	Request Quote

Product Downloads

General

High Power Dichroic Window **Type:**

Physical & Mechanical Properties

3.00 ±0.20 **Thickness (mm):**

22.50 **Clear Aperture CA (mm):**

Diameter (mm):

25.00 +0.0/-0.10

Fine Ground **Edges:**

30' ±10' **Wedge Angle (arcmin):**

Optical Properties

Fused Silica (Corning 7980) **Substrate:**

1.458 **Index of Refraction (n_d):**

10-5 **Surface Quality:**

0 - 5 **Angle of Incidence (°):**

S1: HR 1030nm ± 5nm, AR 940 ± 5nm
S2: AR 940nm & 1030nm ± 5nm **Coating:**

940nm/1030nm **Design Wavelength DWL (nm):**

λ/10 **Surface Flatness (P-V):**

S1: R_p & R_s >99.5% @ 1030nm;
T_p & T_s >98% @ 940nm @ 0 – 5° AOI
S2: T_p & T_s >98% @ 940nm & 1030nm **Coating Specification:**

> 20 J/cm² @ 10ns pulses @ 5 kHz PRF
1MW/cm² CW **Damage Threshold, Reference:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- High Reflectivity at 1030nm and High Transmission at 940nm
- Low Group Delay Dispersion (GDD) <±100fs²
- Dichroic Mirror Ideal for Ytterbium (Yb) Lasers

Yb-Doped Dichroic Mirrors feature a high reflectivity of 99.5% at 1030nm and transmission of 98% at 940nm with wide acceptance angles of 0 – 5°. Featuring wedged substrates that minimize back reflections even at 0° AOI, these mirrors eliminate unwanted feedback in laser systems and are available in either 12.5, 25, or 50mm diameters with a thickness of 3mm. Designed for high power applications utilizing nanosecond pulses, these mirrors are ideal for precision material processing. Yb-Doped Dichroic Mirrors also offer a Low Group Delay Dispersion (GDD) of <±100fs² from 1030nm – 1080nm, making them useful for ultrafast and nonlinear applications including multi-photon microscopy.