


TECHSPEC® 25mm Dia. x 200mm FL, NIR I Coated, Achromatic Lens



Stock **#22-496** ☐ In Stock
[Other Coating Options](#)

1 **C\$182.00**

ADD TO CART

Qty 1-5
C\$182.00
Qty 6+
C\$145.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
200.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 193.761
Focal Length Specification Wavelength (nm) : 880.00
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 6.00 ±0.10
Center Thickness CT 2 (mm) : 4.00 ±0.10
Radius R₁ (mm) : 112.88
Radius R₂ (mm) : -112.88
Radius R₃ (mm) : -1415.62
Edge Thickness ET (mm) : 9.25
Substrate : ☐ N-LAK22 / N-SF6
Surface Quality : 40-20
f/# : 8.00
Numerical Aperture NA : 0.06
Coating : NIR I (600-1050nm)
Coating Specification : R _{avg} ≤0.5% @ 600 - 1050nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 600 - 1050

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View