

TECHSPEC® 25mm Dia x 20mm FL 3-12μm Coated, Ge Aspheric Lens



Stock **#89-609** ☐ In Stock
[Other Coating Options](#)

1 **C\$1,391.60**

ADD TO CART

Qty 1-5
C\$1,391.60
Qty 6+
C\$1,113.28
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
20.00 @4000nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm):

19.08
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.5
Center Thickness CT (mm): 3.70 ±0.10
f/#: 0.79
Bevel: Protective bevel as needed
Edges: Diamond Turned
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant