

[See all 22 Products in Family](#)

25mm Dia. x 25mm FL Protected Aluminum, Concave Mirror



Stock **#43-465** [CONTACT US](#)

-

 1

+

C\$76^{.30}

ADD TO CART

Volume Pricing	
Qty 1-49	C\$76.30 each
Qty 50-99	C\$64.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Spherical Mirror

Physical & Mechanical Properties

Thickness Tolerance (mm):

±0.5

Diameter (mm):

25.00 ±0.50

Clear Aperture (%):

90

3.0	Edge Thickness ET (mm):
Optical Properties	
Metal	Coating Type:
Protected Aluminum (400-2000nm)	Coating:
400 - 2000	Wavelength Range (nm):
25.00	Effective Focal Length EFL (mm):
N-BK7	Substrate:
f/1	Aperture (f/#):
R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm	Coating Specification:
±2	Focal Length Tolerance (%):
50.00	Radius R _i (mm):
80-50	Surface Quality:
50.00	Radius of Curvature (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

Technical Information

