

TECHSPEC[®] 25mm Dia x 25mm FL, Uncoated, 1550nm High Precision Aspheric Lens



TECHSPEC[®] High Precision Aspheric Lenses

Stock **#17-420** **1 In Stock**

☐ [Other Coating Options](#)

-

1

+

C\$1,048⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$1,048.60 each
Qty 6-10	C\$943.60 each
Qty 11+	C\$880.60 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens

Type:

3D Surface Profile included with uncoated lenses

Note:

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.0/-0.025	
<2.5	Centering (arcmin):
22.5	Clear Aperture CA (mm):
4.25	Edge Thickness ET (mm):
8.50 ±0.1	Center Thickness CT (mm):
Protective as needed	Bevel:
Plano	Shape of Back Surface:
Optical Properties	
25.00 @ 1550nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
20.18 @ 1550nm	Back Focal Length BFL (mm):
N-SF6	Substrate: □
1550	Aspheric Design Wavelength (nm):
λ/40	Asphere Figure Error, RMS @ 632.8nm:
Uncoated	Coating:
40-20	Surface Quality:
1	f/#:
Infinite	Conjugate Distance:
40.00	Power (diopters):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Precision Aspheric Surface
- 3D Surface Profiles Included with Uncoated Lenses
- Uncoated and <0.25% Reflectance V-Coat Available

TECHSPEC® High Precision Aspheric Lenses guarantee better than λ/40 wave aspheric figure error. Achieved via precision magneto-rheological finishing (MRF), these aspheres offer high numerical apertures with diameters ranging from 15 to 50mm and are ideal for a variety of imaging and low light level applications. Each TECHSPEC High Precision Aspheric Lens is individually measured. 3D surface profiles are included with uncoated lenses. For diffraction-limited aspheres designed at specific Nd:YAG laser wavelengths, see our [TECHSPEC High Precision Laser Grade Aspheric Lenses](#).

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts