

TECHSPEC® 25mm Dia. x 300mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-649-INK** 3-5 DAYS

[Other Coating Options](#)



1



C\$168.00

ADD TO CART

Qty 1-5

C\$168.00

Qty 6+

C\$134.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
300.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 297.73
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 5.50 ±0.20
Center Thickness CT 1 (mm): 3.00 ±0.10
Center Thickness CT 2 (mm): 2.50 ±0.10
Radius R₁ (mm): 184.84
Radius R₂ (mm): -134.06
Radius R₃ (mm): -393.98
Edge Thickness ET (mm): 4.88
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 12.00
Numerical Aperture NA: 0.04
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View