

TECHSPEC® 25mm Dia. x 50mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock **#65-976** ☐ In Stock

1 **C\$220.50**

ADD TO CART

Qty 1-5

C\$220.50

Qty 6+

C\$176.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 44.74
Focal Length Specification Wavelength (nm): 405.00
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 10.50 ±0.20
Center Thickness CT 1 (mm): 8.00 ±0.10
Center Thickness CT 2 (mm): 2.50 ±0.10
Radius R₁ (mm): 30.03
Radius R₂ (mm): -24.15
Radius R₃ (mm): -63.90
Edge Thickness ET (mm): 6.54
Substrate: ☐ N-FK5 / F2HT
Surface Quality: 40-20
f/#: 2
Numerical Aperture NA: 0.25
Coating: UV-VIS (345-700nm)
Coating Specification: R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 345 - 700

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Compliant