

TECHSPEC® 25mm Dia. x 50mm FL, NIR II Coated, Achromatic Lens



Stock **#45-803** ☐ In Stock
[Other Coating Options](#)

1 **C\$186.20**

ADD TO CART

Qty 1-5
C\$186.20
Qty 6+
C\$149.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 43.29
Focal Length Specification Wavelength (nm): 880.00
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 12.00 ±0.20
Center Thickness CT 1 (mm): 8.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R₁ (mm): 31.69
Radius R₂ (mm): -28.45
Radius R₃ (mm): -161.05
Edge Thickness ET (mm): 8.94
Substrate: ☐ N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 750 - 1550

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View