

TECHSPEC® 25mm Dia. x 400mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-650-INK** ☐ In Stock
[Other Coating Options](#)

1 **C\$168.00**

ADD TO CART

Qty 1-5
C\$168.00
Qty 6+
C\$134.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
400.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 397.84
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.50 ±0.20
Center Thickness CT 1 (mm) : 3.00 ±0.10
Center Thickness CT 2 (mm) : 2.50 ±0.10
Radius R₁ (mm) : 244.65
Radius R₂ (mm) : -179.62
Radius R₃ (mm) : -534.10
Edge Thickness ET (mm) : 5.03
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 16.00
Numerical Aperture NA : 0.03
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View