

TECHSPEC[®] 25mm Dia. x 75mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock #65-978 ☐ In Stock

-

1

+

C\$220.50

ADD TO CART

Qty 1-5

C\$220.50

Qty 6+

C\$176.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
75.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 71.09
Focal Length Specification Wavelength (nm) : 405.00
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 8.00 ±0.20
Center Thickness CT 1 (mm) : 5.50 ±0.10
Center Thickness CT 2 (mm) : 2.50 ±0.10
Radius R₁ (mm) : 45.50
Radius R₂ (mm) : -36.34
Radius R₃ (mm) : -96.60
Edge Thickness ET (mm) : 5.44
Substrate : ☐ N-FK5 / F2HT
Surface Quality : 40-20
f/# : 3
Numerical Aperture NA : 0.17
Coating : UV-VIS (345-700nm)
Coating Specification : R _{avg} ≤1.5% @ 345 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 345 - 700

Regulatory Compliance

RoHS 2015 : Exempt
Certificate of Conformance : View
Reach 235 : Compliant