

[See all 14 Products in Family](#)

TECHSPEC[®] 25mm Dia. x -50mm FL, UV-AR Coated, UV DCV Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock **#48-330 5 In Stock**

☐ [Other Coating Options](#)

-

1

+

C\$239⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$239.40 each
Qty 6-25	C\$191.80 each
Qty 26-49	C\$179.20 each
Need More?	Request Quote

Product Downloads

General	
Double-Concave Lens	Type:
Max. Flat Annulus is 0.3mm	Note:

Physical & Mechanical Properties	
25.00 +0.0/-0.025	Diameter (mm):
2.50	Center Thickness CT (mm):
±0.10	Center Thickness Tolerance (mm):
<1	Centering (arcmin):
24.0	Clear Aperture CA (mm):
5.78	Edge Thickness ET (mm):
Optical Properties	
-50.00	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate: ☐
2.00	f/#:
0.25	Numerical Aperture NA:
UV-AR (250-425nm)	Coating:
250 - 425	Wavelength Range (nm):
-50.85	Back Focal Length BFL (mm):
R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm	Coating Specification:
587.6	Focal Length Specification Wavelength (nm):
±2	Focal Length Tolerance (%):
-46.23	Radius R ₁ =R ₂ (mm):
40-20	Surface Quality:
3 J/cm ² @ 355nm, 10ns	Damage Threshold, Reference: ☐
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details


- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Wavelength Range of 200 - 2200nm
- Popular UV-AR Coating Option Available

TECHSPEC® UV Fused Silica Double-Concave (DCV) Lenses are manufactured utilizing state-of-the-art CNC equipment. Zygo’s GPI-XP Interferometer is used to ensure the surface accuracy and performance of these optics. UV Grade lenses are precision manufactured using research-grade synthetic fused silica. TECHSPEC® UV Fused Silica Double-Concave (DCV) Lenses, in addition to providing excellent transmission characteristics and higher operating temperatures, synthetic fused silica lenses also exhibit exceptional inclusion specification and chemical purity. These lenses make a superior choice for many laser and imaging applications, particularly those involving ultraviolet wavelengths. A broadband anti-reflection coating is available for optimized throughput in the ultraviolet spectrum.





Technical Information






UV FS Transmission Curve



FUSED SILICA																													
Uncoated Fused Silica Typical Transmission <table border="1"><caption>Approximate data for Uncoated Fused Silica</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>92</td></tr><tr><td>400</td><td>94</td></tr><tr><td>600</td><td>94</td></tr><tr><td>800</td><td>94</td></tr><tr><td>1000</td><td>94</td></tr><tr><td>1200</td><td>94</td></tr><tr><td>1400</td><td>92</td></tr><tr><td>1600</td><td>94</td></tr><tr><td>1800</td><td>94</td></tr><tr><td>2000</td><td>94</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table> Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra. Click Here to Download Data	Wavelength (nm)	Transmittance (%)	200	92	400	94	600	94	800	94	1000	94	1200	94	1400	92	1600	94	1800	94	2000	94	2200	90					
Wavelength (nm)	Transmittance (%)																												
200	92																												
400	94																												
600	94																												
800	94																												
1000	94																												
1200	94																												
1400	92																												
1600	94																												
1800	94																												
2000	94																												
2200	90																												
Fused Silica with MgF₂ Coating Typical Transmission <table border="1"><caption>Approximate data for Fused Silica with MgF2 Coating</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>94</td></tr><tr><td>400</td><td>97</td></tr><tr><td>600</td><td>97</td></tr><tr><td>800</td><td>96</td></tr><tr><td>1000</td><td>96</td></tr><tr><td>1200</td><td>96</td></tr><tr><td>1400</td><td>93</td></tr><tr><td>1600</td><td>95</td></tr><tr><td>1800</td><td>95</td></tr><tr><td>2000</td><td>95</td></tr><tr><td>2200</td><td>90</td></tr></tbody></table> Typical transmission of a 3mm thick fused silica window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	Wavelength (nm)	Transmittance (%)	200	94	400	97	600	97	800	96	1000	96	1200	96	1400	93	1600	95	1800	95	2000	95	2200	90					
Wavelength (nm)	Transmittance (%)																												
200	94																												
400	97																												
600	97																												
800	96																												
1000	96																												
1200	96																												
1400	93																												
1600	95																												
1800	95																												
2000	95																												
2200	90																												
Fused Silica with UV-AR Coating Typical Transmission <table border="1"><caption>Approximate data for Fused Silica with UV-AR Coating</caption><thead><tr><th>Wavelength (nm)</th><th>Transmittance (%)</th></tr></thead><tbody><tr><td>200</td><td>70</td></tr><tr><td>250</td><td>99</td></tr><tr><td>400</td><td>99</td></tr><tr><td>425</td><td>100</td></tr><tr><td>600</td><td>99</td></tr><tr><td>800</td><td>95</td></tr><tr><td>1000</td><td>85</td></tr><tr><td>1200</td><td>78</td></tr><tr><td>1400</td><td>75</td></tr><tr><td>1600</td><td>75</td></tr><tr><td>1800</td><td>75</td></tr><tr><td>2000</td><td>76</td></tr><tr><td>2200</td><td>77</td></tr></tbody></table> Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	Wavelength (nm)	Transmittance (%)	200	70	250	99	400	99	425	100	600	99	800	95	1000	85	1200	78	1400	75	1600	75	1800	75	2000	76	2200	77	
Wavelength (nm)	Transmittance (%)																												
200	70																												
250	99																												
400	99																												
425	100																												
600	99																												
800	95																												
1000	85																												
1200	78																												
1400	75																												
1600	75																												
1800	75																												
2000	76																												
2200	77																												

	
Fused Silica with UV-VIS Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}$$R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-EXT Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS-NIR Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}$$R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Fused Silica with VIS 0° Coating Typical Transmission 	Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data

wavelength (nm)	
Fused Silica with YAG-BBAR Coating Typical Transmission  Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\%$ @ 532nm $R_{abs} \leq 0.25\%$ @ 1064nm $R_{avg} \leq 1.0\%$ @ 500 - 1100nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	
Fused Silica with NIR I Coating Typical Transmission  Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 600 - 1050nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	
Fused Silica with NIR II Coating Typical Transmission  Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 1.5\%$ @ 750 - 800nm $R_{abs} \leq 1.0\%$ @ 800 - 1550nm $R_{avg} \leq 0.7\%$ @ 750 - 1550nm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts