

25mm Dia x -7.75mm FL Protected Gold Coated, Convex Mirror



Stock **#64-074** ☐ In Stock

-

1

+

C\$70.70

ADD TO CART

Qty 1-5
C\$70.70
Qty 6+
C\$63.70
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Focal Length FL (mm):
-7.75

Center Thickness CT (mm):
8.06

Clear Aperture (%):
90

Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Edge Thickness ET (mm): 1.73
Focal Length Tolerance (%): ±2
Radius R (mm): 15.50
Substrate: ☐ N-BK7
Surface Quality: 60-40
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant