

TECHSPEC® 25mm Dia. x 85mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-359** ☐ In Stock
[Other Coating Options](#)

1 **C\$165.20**

ADD TO CART

Qty 1-5
C\$165.20
Qty 6+
C\$132.30
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
85.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 81.21
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 8.01 ±0.20
Center Thickness CT 1 (mm) : 5.01 ±0.10
Center Thickness CT 2 (mm) : 3.00 ±0.10
Radius R₁ (mm) : 55.68
Radius R₂ (mm) : -38.37
Radius R₃ (mm) : -146.45
Edge Thickness ET (mm) : 6.05
Substrate : ☐ N-SK11 / N-SF5
Surface Quality : 40-20
f/# : 3.4
Numerical Aperture NA : 0.15
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View