

[See all 12 Products in Family](#)

**TECHSPEC® 25mm Dia., 3mm Thick, Uncoated, Magnesium Fluoride Window**



Magnesium Fluoride (MgF<sub>2</sub>) Windows

Stock **#64-094** **8 In Stock**

C\$485<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$485.80 each                |
| Qty 11-25      | C\$429.80 each                |
| Qty 26-49      | C\$404.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Type:  
Protective Window

Type of Window:  
Crystal

**Physical & Mechanical Properties**

Clear Aperture CA (mm):  
22.50

|                      |  |
|----------------------|--|
| 25.00 +0.0/-0.1      | <b>Diameter (mm):</b>                      |
| 3.00 ±0.1            | <b>Thickness (mm):</b>                     |
| <1                   | <b>Parallelism (arcmin):</b>               |
| Protective as needed | <b>Bevel:</b>                              |
| 90                   | <b>Clear Aperture (%):</b>                 |
| Fine Ground          | <b>Edges:</b>                              |
| 0.27                 | <b>Poisson's Ratio:</b>                    |
| 138                  | <b>Young's Modulus (GPa):</b>              |
| 415.00               | <b>Knoop Hardness (kg/mm<sup>2</sup>):</b> |

## Optical Properties

|  |   |
|--|---|
| Uncoated                               | <b>Coating:</b>                             |
| Magnesium Fluoride (MgF <sub>2</sub> ) | <b>Substrate:</b> <input type="checkbox"/>  |
| 1.377                                  | <b>Index of Refraction (n<sub>d</sub>):</b> |
| 40-20                                  | <b>Surface Quality:</b>                     |
| 106.22                                 | <b>Abbe Number (v<sub>d</sub>):</b>         |
| 120 - 7000                             | <b>Wavelength Range (nm):</b>               |
| λ/2                                    | <b>Surface Flatness (P-V):</b>              |

## Material Properties

|      |   |
|------|---|
| 3.18 | <b>Density (g/cm<sup>3</sup>):</b>                                |
| 13.7 | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |

## Regulatory Compliance

|                  |                                    |
|------------------|------------------------------------|
| <b>Compliant</b> | <b>RoHS 2015:</b>                  |
| <b>Compliant</b> | <b>Reach 219:</b>                  |
| <b>View</b>      | <b>Certificate of Conformance:</b> |

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Excellent Transmission from 120nm to 7µm
- Rugged and Durable
- Resistant to Chemical Etching

TECHSPEC® Magnesium Fluoride (MgF<sub>2</sub>) Windows offer excellent broadband transmission from the deep-UV to the mid-infrared. DUV transmission makes them ideal for use at the Hydrogen Lyman-alpha line and for UV radiation sources and receivers, as well as excimer laser applications. MgF<sub>2</sub> is a rugged material resistant to chemical etching, laser damage, and mechanical and thermal shock. TECHSPEC® Magnesium Fluoride (MgF<sub>2</sub>) Windows have a Knoop Hardness of 415 and index of refraction of 1.38. The windows are offered in diameters ranging from 5 to 75mm.

## Technical Information



## Compatible Mounts

---