


**TECHSPEC® 25mm Dia. x -25mm FL, NIR I Coated, Double-Concave Lens**



Stock **#49-550** ☐ In Stock  
[Other Coating Options](#)

1  **C\$63.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| C\$63.00                      |
| Qty 10+                       |
| C\$56.70                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
25.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**  
-25.00

|                                                                                                            |
|------------------------------------------------------------------------------------------------------------|
| <div>Substrate: <div><div></div></div><div>N-SF11</div></div>                                              |
| <div>f/#:<div>1.00</div></div>                                                                             |
| <div>Numerical Aperture NA:<div>0.50</div></div>                                                           |
| <div>Coating:<div>NIR I (600-1050nm)</div></div>                                                           |
| <div>Type:<div>Double-Concave Lens</div></div>                                                             |
| <div>Wavelength Range (nm):<div>600 - 1050</div></div>                                                     |
| <div>Back Focal Length BFL (mm):<div>-25.69</div></div>                                                    |
| <div>Bevel:<div>Protective bevel as needed</div></div>                                                     |
| <div>Center Thickness CT (mm):<div>2.50</div></div>                                                        |
| <div>Center Thickness Tolerance (mm):<div>±0.10</div></div>                                                |
| <div>Centering (arcmin):<div>&lt;1</div></div>                                                             |
| <div>Clear Aperture CA (mm):<div>24.00</div></div>                                                         |
| <div>Coating Specification:<div>R<sub>avg</sub> ≤0.5% @ 600 - 1050nm</div></div>                           |
| <div>Edge Thickness ET (mm):<div>6.05</div></div>                                                          |
| <div>Focal Length Specification Wavelength (nm):<div>587.6</div></div>                                     |
| <div>Focal Length Tolerance (%):<div>±1</div></div>                                                        |
| <div>Radius R<sub>1</sub>=R<sub>2</sub> (mm):<div>-39.78</div></div>                                       |
| <div>Surface Quality:<div>40-20</div></div>                                                                |
| <div>Damage Threshold, By Design: <div><div></div></div><div>7 J/cm<sup>2</sup> @ 1064nm, 10ns</div></div> |
| <div>Power (P-V) @ 632.8nm:<div>1.5λ</div></div>                                                           |
| <div>Irregularity (P-V) @ 632.8nm:<div>λ/4</div></div>                                                     |

## Regulatory Compliance

|                                                       |
|-------------------------------------------------------|
| <div>RoHS 2015:<div>Compliant</div></div>             |
| <div>Certificate of Conformance:<div>View</div></div> |
| <div>Reach 235:<div>Compliant</div></div>             |