

TECHSPEC[®] 25mm Diameter x 3.3mm Thickness, Uncoated, BOROFLOAT[®] Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#43-892** 20+ In Stock

-

1

+

C\$39^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$39.20 each
Qty 6-25	C\$30.80 each
Qty 26-99	C\$29.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Protective Window

Physical & Mechanical Properties

Clear Aperture CA (mm):

22.50

Diameter (mm):

25.00 ±0.5	
3.30 ±0.2	Thickness (mm):
Protective as needed	Bevel:
≥90	Clear Aperture (%):
Ground	Edges:
0.20	Poisson's Ratio:
64	Young's Modulus (GPa):
480.00	Knoop Hardness (kg/mm²):

Optical Properties	
Uncoated	Coating:
BOROFLOAT®	Substrate: ☐
1.472	Index of Refraction (n _d):
80-50	Surface Quality:
90	Transmission (%):
65.41	Abbe Number (v _d):
350 - 2000	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):

Material Properties	
2.23	Density (g/cm³):
525	Transformation Temperature (°C):

Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
3.25 (+20 to +300°C)

Environmental & Durability Factors	
1 hour @ 500; >100 hours @ 450	Operating Temperature (°C):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	Resistance to Temperature Difference (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	Thermal Shock (K):


Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Low Coefficient of Thermal Expansion
 - Visible to Near Infrared Transmission
 - High Resistance to Thermal Shock
- TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts