

TECHSPEC[®] 25mm Diameter x 38mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCXLenses

Stock **#67-094** **20+ In Stock**

☐ [Other Coating Options](#)

-

1

+

C\$282^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$282.80 each
Qty 6-25	C\$225.40 each
Qty 26-49	C\$211.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

25.00 +0.00/-0.10

Centering (arcmin):

<1	
7.25 ±0.10	Center Thickness CT (mm):
1.96	Edge Thickness ET (mm):
22.5	Clear Aperture CA (mm):
Protective as needed	Bevel:
Optical Properties	
38.00 @ 587.6nm	Effective Focal Length EFL (mm):
33.03	Back Focal Length BFL (mm):
Uncoated	Coating:
Fused Silica (Corning 7980)	Substrate: □
20-10	Surface Quality:
λ	Power (P-V) @ 632.8nm:
λ/10	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
17.42	Radius R ₁ (mm):
1.52	f/#:
0.33	Numerical Aperture NA:
200 - 2200	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

• Guaranteed Laser Damage Threshold

• 10-5 Surface Quality

• λ/10 Surface Accuracy

TECHSPEC® Laser Grade PCXLenses are designed for high energyNd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring λ/10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.


LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts