

**TECHSPEC® 25mm FL f/2.5, Blue Series IR-Cut M12 Lens**



Stock #24-470 **14 In Stock**

- 1 + C\$161<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-49       | C\$161.00 each                |
| Qty 50+        | C\$127.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Blue Series **Product Family:**

M12 Imaging Lens **Type:**

Yes **IR Cut Filter:**

**Special Type of Lens:**

## Physical & Mechanical Properties

|       |                               |
|-------|-------------------------------|
| Fixed | <b>Iris Option:</b>           |
| 30.00 | <b>Length (mm):</b>           |
| 18    | <b>Maximum Diameter (mm):</b> |
| 18    | <b>Outer Diameter (mm):</b>   |
| 12    | <b>Weight (g):</b>            |

## Optical Properties

**Horizontal Field of View @ Max Sensor Format:**  
16.2°

**Field of View at Max Sensor Format:**  
Horizontal: 40.0mm - 16.2°  
Vertical: 26.5mm - 10.9°  
Diagonal: 44.3mm - 18°

**Horizontal Field of View, 1.2" Sensor:**  
35.4mm - 14.5°

**Horizontal Field of View, 1/1.8" Sensor:**  
40.0mm - 16.2°

**Horizontal Field of View, 1/2.5" Sensor:**  
32.1mm - 13.1°

**Horizontal Field of View, 1/3" Sensor:**  
26.5mm - 10.9°

**Horizontal Field of View, 1/4" Sensor:**  
19.9mm - 8.2°

**Maximum Image Circle (mm):**  
9.00

**Numerical Aperture NA, Object Side:**  
0.0322

**Number of Elements (Groups):**  
6(5)

**Wavelength Range (nm):**  
400 - 700

**Focal Length FL (mm):**  
25.00

**Working Distance (mm):**  
150 - ∞

**Aperture (f#):**  
f/2.5

**Distortion (%):**  
0.59 @ Full Field

**Back Focal Length BFL (mm):**  
8.5 - 6.5

**Coating Specification:**  
λ/4 MgF<sub>2</sub> @ 550nm

**Entrance Pupil Position (mm):**  
4.15

**Object Space Principal Plane (mm):**  
11.90

**Image Space Principal Plane (mm):**  
-19.03

**Maximum Distortion (%):**  
-0.59

**Exit Pupil Position (mm):**  
-30.25

**Lens Wavelength Range:**  
VIS (IR-Cut Filter)

## Sensor

|        |                               |
|--------|-------------------------------|
| 1/1.8" | <b>Maximum Sensor Format:</b> |
| 1.40   | <b>Pixel Size (μm):</b>       |

## Threading & Mounting

|     |                       |
|-----|-----------------------|
| N/A | <b>Filter Thread:</b> |
|     | <b>Mount:</b>         |

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

## Product Details

- Up to 1/2", S-Mount Lens
- Up to 5 MegaPixels, 1.4µm Pixel Size Sensors
- High Resolution Board Camera Lens Optimized for Close WD
- 2mm to 35mm Focal Length
- **Ruggedized Designs** Also Available

TECHSPEC® Blue Series M12 Lenses feature high resolution performance, along with the same great versatility of our **TECHSPEC® Green Series M12 Lenses**. Each lens consists of several precision glass elements mounted in a compact, aluminum housing. These lenses can connect to C-Mount cameras using the M12 x0.5 Adapter for C-Mount Cameras (**#53-675**) or the M12 x0.5 C-Mount Adapter with Rubber O-Ring (**#59-241**) for vibration-sensitive environments. TECHSPEC® Blue Series M12 Lenses are ideal for automotive, industrial, and medical imaging application. Prescription data is available by submitting a **Request for Prescription Form**.

**Note:** Compatible **TECHSPEC® M12 Imaging Lens Accessories** available.

Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** **Stabilized ruggedization** versions of our Blue Series M12 Lenses, utilizing the same optics.
- **Green Series M12 Lenses:** Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.

## Technical Information

| Focal Length | A      | B      | C*             | D      |
|--------------|--------|--------|----------------|--------|
| 2.0mm        | 18.0mm | 21.7mm | 2.26mm         | 4.75mm |
| 3.0mm        | 14.0mm | 17.1mm | 4.8 - 4.7mm    | 5.8mm  |
| 4.0mm        | 14.0mm | 19.7mm | 6.1 - 6.0mm    | 4.4mm  |
| 5.0mm        | 14.0mm | 14.6mm | 4.0 - 3.9mm    | 3.7mm  |
| 6.0mm        | 14.0mm | 14.1mm | 6.9 - 6.8mm    | 4.5mm  |
| 8.0mm        | 14.0mm | 12.3mm | 8.8 - 8.6mm    | 3.7mm  |
| 10.0mm       | 14.0mm | 17.0mm | 6.6 - 6.3mm    | 3.7mm  |
| 12.5mm       | 15.0mm | 22.9mm | 10.1 - 9.7mm   | 4.8mm  |
| 17.5mm       | 14.0mm | 20.7mm | 5.8 - 4.9mm    | 7.6mm  |
| 25.0mm       | 18.0mm | 30.0mm | 8.5 - 6.5mm    | 11.5mm |
| 35.0mm       | 18.0mm | 29.5mm | 18.72 - 14.0mm | 14.5mm |

\*Specified for Optimized Working Distance of 150 - 250mm.