

TECHSPEC®

25mm H x 50mm L x 50mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens



Stock #69-732 ☐ In Stock

-

1

+

C\$180.60

ADD TO CART

Qty 1-5
C\$180.60
Qty 6+
C\$144.20
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate: ☐
[N-BK7](#)

f/#:
2

Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 47.20
Center Thickness CT (mm): 4.24
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.93
Surface Quality: 60-40
Damage Threshold, Reference:  5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant