

26.5mm Dia. x 18mm FL, Uncoated, Molded Condenser Lens with Smooth Diffuser



Molded Diffuse Aspheric Condenser Lenses

Stock **#22-680** ☐ In Stock



1



C\$49.00

ADD TO CART

Qty 1-10

C\$49.00

Qty 11+

C\$44.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

26.50 ±0.20

Effective Focal Length EFL (mm):

18.00

Numerical Aperture NA:

0.67

Back Focal Length BFL (mm):

10.50
Substrate: Liba2000+
Focal Length Tolerance (%) : ±7
Coating: Uncoated
Centering (arcmin) : ≤25
Surface Quality: As Molded
Clear Aperture CA (mm) : 21.60
Edge Thickness ET (mm) : 2.50
Center Thickness CT (mm) : 11.37 ±0.20
f/# : 0.75
Bevel: Protective bevel as needed
Diameter of Asphere (mm) : 24
Radius R₂ (mm) : Plano
Shape of Back Surface : Plano
Wavelength Range (nm) : 350 - 2000
Conjugate Distance : Infinite
Note: Maximum of 5 imperfections allowed with an area of 0.8mm, per ISO 10110-7 specification of 5/5 x0.63. Click here for more information on the ISO 10110 surface quality specification.
Grit: Smooth

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant