

[See all 5 Products in Family](#)

2mm FL, 632nm, Visible Metalens Plate



Stock #86-932 NEW CONTACT US

-
1
+
C\$1,050⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$1,050.00 each
Qty 10+	C\$945.00 each
Need More?	Request Quote

Product Downloads

General

Note:
Black absorptive aperture applied to metasurface

Physical & Mechanical Properties

Dimensional Tolerance (mm):
+/-0.2

Thickness (mm):
0.70 ±0.07

Outer Dimensions (mm):
20.0 x 20.0

Inner Diameter (mm):

Optical Properties

Effective Focal Length EFL (mm):

2.00 ±2%

Substrate:

Eagle XG

Numerical Aperture NA:

0.707

Coating:

Broadband 420-670nm AR Coating, backside
Protective Overcoat, frontside

Coating Specification:

Broadband 420-670nm AR-Coating (Back surface only)
 $R_{\text{abs}} \leq 1\%$ from 420-670nm
 $R_{\text{avg}} \leq 0.4\%$ from 420-670nm

Design Wavelength DWL (nm):

632

Index of Refraction (n_d):

1.5198 (435.8 nm), 1.5078 (643.8 nm)

Transmission (%):

53

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Flat, Space Saving Alternative to Traditional Lenses
- Nanostructure Design Enables Efficient Manipulation of Light
- Compact 0.7mm Thickness for Easy Integration into a Variety of Applications

Visible Meta-Lens Plates are designed with an innovative nanostructure design to manipulate and focus light, offering a highly compact and high-performance alternative to traditional curved lenses. Featuring ultra-thin Eagle XG substrates, these lens plates are available for 532nm and 632nm design wavelengths in a range of focal lengths. These meta-lenses are available in a single lens construction, where an individual meta-lens is centered on the plate and surrounded by an absorptive aperture to reduce stray light, or an array construction, where one of each of the four smaller Meta-lenses are arranged on a single plate for versatility. Visible Meta-Lens Plates are ideal for low SWaP, LIDAR, imaging, and beam shaping applications.

Note: The Meta-lens surface is very delicate, and contact should be avoided during cleaning and handling. Visible Meta-lens Plates should be cleaned only using compressed air.