

TECHSPEC® 2mm Dia. x 4.0mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#65-568** ☒ In Stock

[Other Coating Options](#)

1

C\$326.20

ADD TO CART

Qty 1-5

C\$326.20

Qty 6+

C\$261.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
2.00 +0.0/-0.025

Effective Focal Length EFL (mm):

4.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 2.92
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 1.6
Centering (arcmin): 30-45
Center Thickness CT (mm): 2.00 ±0.10
Center Thickness CT 1 (mm): 1.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R ₁ (mm): 2.26
Radius R ₂ (mm): -2.26
Radius R ₃ (mm): -10.00
Edge Thickness ET (mm): 1.72
Substrate:  N-PSK53A / N-LASP9
Surface Quality: 20-10
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View