

# 3" Length, 8-32 and 1/4-20, Steel Post



Stock **#72-785** NEW [CONTACT US](#)

-

1

+

C\$9<sup>-10</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$9.10 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

English

Type:

Physical & Mechanical Properties

|      |                    |
|------|--------------------|
| 12.7 | Diameter (mm):     |
| 0.5  | Diameter (inches): |
| 76.2 | Length (mm):       |
|      | Length (inches):   |

Threading & Mounting

Thread 1: 8-32  
Thread 2: 1/4 - 20

Male Thread:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 250:

Product Details

- English or Metric Versions Options Available
  - Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
  - Removable Top and Bottom Set Screws Available
- Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/1/4-20 for English) are laser-engraved on the ends of each post for quick identification and integration.
- Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.