

TECHSPEC® 2X, 0.15 NA, UCf Objective



Stock #36-278 ☐ In Stock

-

1

+

C\$273.00

ADD TO CART

Qty 1-2

C\$273.00

Qty 3+

C\$252.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
4.4

Horizontal Field of View, 1.1" Sensor:
7.04

Focal Length FL (mm):
8.00

Length (mm):
10.80

Magnification: 2X
Maximum Diameter (mm): 29.0
Maximum Sensor Format: 1.1"
Mount: C-Mount
Numerical Aperture NA: 0.15
Mounting Threads: C-Mount
Type: Fluorite
Resolving Power (μm): 4.44
Depth of Field (μm): 12.00
Working Distance (mm): 11.3
Weight (g): 19
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Manufacturer: Edmund Optics®
Field Number (mm): 17.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View