

304.8mm Length, M6 and M6, Steel Post



Stock **#72-780** NEW **20+ In Stock**

-

1

+

C\$18^{.90}

ADD TO CART

Volume Pricing	
Qty 1+	C\$18.90 each
Need More?	Request Quote

Product Downloads

General

	Type:
Metric	

Physical & Mechanical Properties

	Diameter (mm):
12.7	
	Diameter (inches):
0.5	
	Length (mm):
304.8	
	Length (inches):

Threading & Mounting	
Thread 1: M6 x 1 Thread 2: M6 x 1	Male Thread:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- English or Metric Versions Options Available
 - Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
 - Removable Top and Bottom Set Screws Available
- Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/1/4-20 for English) are laser-engraved on the ends of each post for quick identification and integration.
- Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.