

TECHSPEC® 30mm Dia., 0.66 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-433** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$525.00

ADD TO CART

Qty 1-5

C\$525.00

Qty 6+

C\$420.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
30.00 +0.00/-0.025

Effective Focal Length EFL (mm):
22.50 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 13.53
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27.00
Edge Thickness ET (mm): 6.62
Center Thickness CT (mm): 15.00 ±0.10
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 44.44

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant