

TECHSPEC[®] 30.0mm Dia. x 60.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock #48-234-INK 3-5 DAYS

[Other Coating Options](#)

-

1

+

C\$84.70

ADD TO CART

Qty 1-9

C\$84.70

Qty 10+

C\$76.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
60.00 @ 587.6nm

Back Focal Length BFL (mm): 56.03
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Edge Thickness ET (mm): 2.13
Radius R₁ (mm): 31.01
Clear Aperture CA (mm): 29
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View