

## 304.8mm Length, M4 and M6, Steel Post



Stock #72-770 NEW **14 In Stock**

C\$18<sup>90</sup>

ADD TO CART

### Volume Pricing

Qty 1+	C\$18.90 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric Type:

### Physical & Mechanical Properties

±0.1 Length Tolerance (mm):

12 Length (inches):

304.80 Length (mm):

Diameter (inches):

0.5

12.70 **Diameter (mm):**

-0.02/-0.05 **Diameter Tolerance (mm):**

### Threading & Mounting

**Male Thread:**  
Thread 1: M4 x0.7  
Thread 2: M6 x1

### Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
[Compliant](#)

## Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x0.7/M6 x 1.0 for Metric; 8-32<sup>1/4</sup>-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.