

TECHSPEC® 30mm Dia., 0.58 NA, 600-1050nm Coated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#16-286** ☐ In Stock

☐ [Other Coating Options](#)

1 **C\$483.00**

ADD TO CART

Qty 1-5

C\$483.00

Qty 6+

C\$386.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 +0.00/-0.10

Effective Focal Length EFL (mm):
26.00 @ 780nm

Numerical Aperture NA:
0.58

Back Focal Length BFL (mm): 20.57
Substrate: S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: NIR+ (600-1050nm)
Coating Specification: R _{avg} < 0.5% @ 600 - 1050nm @ 0° ±30° AOI R _{abs} < 1.5% @ 600 - 1050nm @ 0° ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 27
Edge Thickness ET (mm): 3.82
Center Thickness CT (mm): 9.65 ±0.10
f/#: 0.87
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 38.46

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View