

TECHSPEC® 3.0mm Dia. x 12.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#49-172** [CONTACT US](#)

[Other Coating Options](#)

- 1 +

C\$83.30

ADD TO CART

Qty 1-9
C\$83.30
Qty 10+
C\$74.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Effective Focal Length EFL (mm):
12.00 @ 587.6nm

Back Focal Length BFL (mm): 11.29
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.08 ±0.05
Edge Thickness ET (mm): 0.90
Radius R₁ (mm): 6.20
Clear Aperture CA (mm): 2.5
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant