

TECHSPEC®

3.0mm Dia. x 3.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#45-118** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$79.80

ADD TO CART

Qty 1-9
C\$79.80
Qty 10+
C\$71.75
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Effective Focal Length EFL (mm):
3.00 @ 587.6nm

Back Focal Length BFL (mm): 1.88
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 2.00 ±0.05
Edge Thickness ET (mm): 1.46
Radius R₁ (mm): 2.35
Clear Aperture CA (mm): 2.5
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View