

TECHSPEC® 30mm Dia x 24mm FL, MgF₂ Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock **#15-195** [CONTACT US](#)

[Other Coating Options](#)

[-](#) 1 [+](#)

C\$70.00

ADD TO CART

Qty 1-10

C\$70.00

Qty 11+

C\$61.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.3

Effective Focal Length EFL (mm):
24.00 @ 587.6nm

Numerical Aperture NA:
0.625

Back Focal Length BFL (mm): 14.73
Substrate: Liba2000+
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/5 x0.63; E 0.4 Polished Side: 5/5 x0.25; E 0.4
Clear Aperture CA (mm): 26.78
Edge Thickness ET (mm): 3.21
Center Thickness CT (mm): 14.10 ±0.30
f#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 30.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant