

TECHSPEC® 30mm UV Enhanced Aluminum Coated, N-BK7 Right Angle Prism



Stock #24-183

CONTACT US

-

1

+

C\$210.00

ADD TO CART

Qty 1-5
C\$210.00
Qty 6+
C\$168.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):

N/4

Substrate:

[N-BK7](#)

Surface Quality:

60-40

Length of Legs (mm):

30.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >85% @ 250 - 700nm R _{avg} >89% @ 250 - 450nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 38.19 x 27.00
Length of Hypotenuse (mm): 42.40
Type: Right Angle Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant