


[See all 11 Products in Family](#)

32 x 32mm Laser Diode Mirror



Stock **#31-495** **20+ In Stock**

-

1

+

C\$44^{.80}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$44.80 each
Qty 11-24	C\$35.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Flat Mirror

Physical & Mechanical Properties

Thickness (mm):

6.35

Dimensions (mm):

32.0 x 32.0

Dimensional Tolerance (mm):

±0.25

32.00	Length (mm):
32.00	Width (mm):
Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (500-700nm)	Coating:
633	Design Wavelength DWL (nm):
Float Glass	Substrate: □
R _{abs} >97% @633nm	Coating Specification:
80-50	Surface Quality:


Environmental & Durability Factors	
ML-C-48497A	Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Over 95% Reflectance of Visible Laser Diode Light
 - Ideal for Multiple Reflection Systems
 - Coating Optimized for 633nm at 45° AOI
- Visible Laser Diode Mirrors are specially coated to attain maximum reflection of visible laser diodes. Optimized for 633nm at a 45° angle of incidence, these mirrors provide 97% reflectance versus only 85 - 90% for standard first surface mirrors. This reduced loss is particularly important in multiple reflection systems, where loss can significantly impact system efficiency. Visible Laser Diode Mirrors feature a float glass substrate and are ideal for multiple reflection systems.

Technical Information

Visible Laser Diode Mirror Reflectance at 45°



@ 500nm	95.0%
@ 550nm	97.0%
@ 600nm	97.5%
@ 633nm	97.0%
@ 635nm	97.0%
@ 650nm	96.5%
@ 670nm	96.0%
@ 675nm	95.0%
@ 700nm	94.5%

Quote Your Size

Compatible Mounts

