

TECHSPEC® 30mm Dia. x 60mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-372-INK** 3-5 DAYS

[Other Coating Options](#)



1



C\$215.60

ADD TO CART

Qty 1-5

C\$215.60

Qty 6+

C\$172.55

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
30.00 ±0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 52.50
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 11.46 ±0.20
Center Thickness CT 1 (mm): 8.47 ±0.10
Center Thickness CT 2 (mm): 2.99 ±0.10
Radius R₁ (mm): 32.60
Radius R₂ (mm): -31.81
Radius R₃ (mm): -799.64
Edge Thickness ET (mm): 7.66
Substrate: ☐ N-SSK6 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View